


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: +33(0)5 55 06 87 87 Fax: +33(0)5 55 06 88 88 www.legrand.com

# MyHOME<sup>®</sup> Play Radio wireless motion sensor

#### Cat. No(s): 0 883 09



## 1. USE

Switches on lights connected to radio receivers when motion is detected during the selected time delay.

Sensor range adjustable from 2 to 10 m, time delay adjustable from 1 to 30 min.

Test possible with 5 sec time delay.


Light level threshold adjustable from 1 to 1000 lux.

Can be associated with KNX bridge 0 788 77 for KNX use.

### 2. RANGE

Description	Colour	Cat. No.
Radio wireless motion sensor		0 883 09

#### **3. DIMENSIONS**



## 4. CONNECTION

No need for connection (battery powered)

### **5. TECHNICAL CHARACTERISTICS**

#### 5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies/liquids: IP42

#### 5.2 Materials

Halogen-free
UV resistant
Enclosure material:
polycarbonate
Self-extinguishing:
+ 850°C/30 s

#### **Electrical characteristics**

Powered by 2 x 1.5 V AA batteries, supplied 2.4 GHz radio technology Consumption during use: 0.932 mA/2.796 W Consumption on standby: 0.032 mA/0.096 W

#### 5.3 Climatic characteristics

Operating temperature:  $+5^{\circ}$ C to  $+45^{\circ}$ C storage temperature:  $0^{\circ}$ C to  $+45^{\circ}$ C

#### 6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

.....

### 7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.